


AMG5722 Instruction Manual

Dual System with 2x Independent Channels each of : [Single Channel Video Receive Unit for a Singlemode Fibre Link]



The **AMG5722** is a **DUAL** standalone system which provides two independent channels, each designed to receive one video signal over one Singlemode optical fibre. i.e. a total of two optical fibres.

The **AMG5722** is designed to be powered using an **AMG2001** standalone power supply.

The **AMG5722** is designed to operate with two **AMG5711** single channel video transmit units in a point to point configuration.

Contents

| | |
|--|----------|
| Introduction | 3 |
| Unit Functional Schematic..... | 3 |
| Optical Connection | 3 |
| Connections | 4 |
| Video Output Connections..... | 4 |
| Optical Connections | 4 |
| Power Connection | 4 |
| Front Panel Indicators | 4 |
| Power LED..... | 4 |
| Physical Information | 5 |
| Dimensions | 5 |
| Mounting Details | 5 |
| Removal / replacement from / to the Case | 5 |
| Safety | 5 |
| Maintenance and Repair | 5 |


Introduction

Unit Functional Schematic

The **AMG5722** provides two independent, receive channels.


Each channel receives one video signal from up to two independent **AMG5711** transmit units.

The schematic diagram shows one of the two available channels of the **AMG5722**



Optical Connection

The **AMG5722** connections are illustrated in the following example which shows two **AMG5711** single channel transmit units together with an **AMG5722** configured as a dual channel point to point system.



Connections

Video Output Connections

No. of channels2 independent video channels
Connectors75 ohm BNC Socket.
Output Impedance75 ohm terminated.
Output Level1 Volt p-p nominal
Frequency Response.....10Hz to 7MHz.

Optical Connections

No. of Optical Connections1 per video channel
Optical Fibre Singlemode
Connector SC/PC

Primary Optical Sensitivity-30dBm
Receive Wavelength..... 1310nm

Minimum Optical Dynamic Range20dB.

Power Connection

Connector TypeRemovable 2-pin, 3.81mm, Screw Terminal
Connector Partno.....Phoenix 1803578
Supply Voltage.....+12 to +15 Volts DC
Maximum Power1.5 Watts

Front Panel Indicators

Power LED

| | | | |
|---------------------------|-------|---|----------------------------------|
| Power / Video / Opto..... | Green | - | Video present & opto sync. |
| | R/G | - | Opto sync. but no video present. |
| | Red | - | No opto sync. |
| | Off | - | No power applied to unit. |

Physical Information

Dimensions

Height 112mm
Width 170mm (excluding connectors)
Depth 35mm
Weight 600grams

Mounting Details

The AMG unit is supplied with a clip-on mounting bracket which should be attached to a panel or wall using 2 off 4.0mm screws, see diagram on page 1 for dimensions. The unit is clipped into the mounting bracket, and is then held firmly in position.

Removal / replacement from / to the Case

Note: - The AMG unit PCB is static sensitive. Handle with proper care and use normal electrostatic discharge (ESD) procedures. Use properly grounded protection (for example, wrist straps) when handling the PCB out of the case.

To remove the PCB from the case for example to access a Low Speed Data mode switch, remove the 2 fixing screws on the rear panel and slide the PCB sufficiently out of the case to enable access to the switch.

To replace the PCB into the case, slide the PCB gently into the case, if necessary aligning the board with the appropriate slots.

Safety

AMG Optical Fibre Products use Class 1 laser systems in accordance with EN 60825-2:2000.

It is always advisable to follow good practice when working with optical fibre systems. This includes:

- Do not stare with unprotected eyes or with any unapproved collimating device at fibre ends or connector faces, or point them at other people.
- Use only approved filtered or attenuating viewing aids

For other safety issues and advice on good practice associated with optical fibre systems, please see EN 60825-2:2000 or your local safety officer.

Maintenance and Repair

There are no user serviceable parts within AMG products. See unit data sheet for full specification.

In case of problem or failure, please call your local support centre or contact: **AMG Systems Ltd.** at 3 The Omega Centre, Stratton Business Park, Biggleswade, Beds., SG18 8QB, UK.

| | |
|-------------------|----------------------------|
| Phone | +44 (0) 1767 600 777 |
| Technical Support | +44 (0) 1767 604 491 |
| Email | techsupport@amgsystems.com |

This page is intentionally blank.

This page is intentionally blank.

This page is intentionally blank.